

Data sheet for Braking Module

Article No. :

6SL3201-2AD20-8VA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data	
Rated power P_{DB}	2.75 kW
Rated power, max.	5.50 kW
Activation threshold 230V / 400V	388 V (782 V)
Switch to select 230V / 400V	

Mechanical data	
Net weight	0.7 kg (1.54 lb)
Dimensions	
Width	90 mm (3.54 in)
Height	150 mm (5.91 in)
Depth	88 mm (3.46 in)

General technical specifications	
DC link voltage	DC 250 ... 800 V

Connections	
PE connection	

Current carrying capacity	
DC link busbar 230V / 400V	8.0 A / 5.2 A

BrakeResistor	
Connection cross-section, max.	4.0 mm ² (12 AWG)
Cable length to braking resistor, max.	10.0 m (32.81 ft)

Standards	
Compliance with standards	CE, cULus