

Data sheet

US2:52SC6BF

Metal, keyed selector switch Maintained position, B Cam Operator only Key removable in left position 3 position Key type 501CH (standard) Non-Illuminated UL file E22655 in Vol. 6 (7) Sec. 13 (2)	
design of the product	Actuator round
Enclosure	
number of command points	1
delivery state as a kit	No
Actuator	
design of the actuating element	Key-operated switch
material of the actuating element	metal
type of unlocking device	key unlatching
number of switching positions	3
switch position for key distraction	left
lock make	ILLINOIS
key number	501CH
Front ring	
product component front ring	Yes
design of the front ring	standard
material of the front ring	metal
color of the front ring	chrome
Holder	
material of the holder	Metal
General technical data	
product component	
• light source	No
degree of pollution	1
protection class IP	IP66
operating frequency maximum	600 1/h
Net Weight	0.16 kg
Ambient conditions	
ambient temperature	
• during operation	-35 ... +70 °C
• during storage	-40 ... +85 °C
Installation/ mounting/ dimensions	
shape of the installation opening	round
Further information	
Information on the packaging	https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage	https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,...)	https://www.siemens.com/ic10
Industry Mall (Online ordering system)	https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SC6BF
Cax online generator	https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SC6BF
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	https://support.industry.siemens.com/cs/ww/en/ps/US2:52SC6BF
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SC6BF&lang=en

