

LED lamp, super-bright, yellow, wedge base W2 X 4.6D, rated voltage 24 V AC/DC, operational current 10 mA



Figure similar

General technical data		
product designation		LED lamp, super bright
type of light source		LED
color of the light source		yellow
socket design		W2 x 4.6d
product component		
• series resistor		No
• diode		No
• lamp transformer		No
• light source		Yes
type of voltage of the operating voltage for actuation		AC/DC
operating voltage		
• at AC		
— at 50 Hz rated value	V	24 ... 24
— at 60 Hz rated value	V	24 ... 24
• at DC rated value	V	24 ... 24
relative positive tolerance of the operating voltage	%	10
relative negative tolerance of the operating voltage	%	-15
consumed current for rated value of supply voltage maximum	mA	10
type of electrical connection		Miscellaneous
fastening method		miscellaneous

Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB3901-1RB>
Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB3901-1RB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB3901-1RB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB3901-1RB&lang=en

last modified:

4/2/2025 