



Figure similar

SIMATIC ET 200SP, BaseUnit M0 with 2 slots for accommodating R1-capable Interface module IM 155-6 PN R1 incl. server module

General information	
Product type designation	BU type M0
Supply voltage	
Rated value (DC)	24 V
Hardware configuration	
Slots	
• Number of slots	2
Potential separation	
between backplane bus and supply voltage	Yes
Isolation	
Isolation tested with	707 V DC (type test)
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m
Dimensions	
Width	100 mm
Height	141 mm
Depth	29 mm
Weights	
Weight, approx.	142 g
Classifications	

	Version	Classification
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598

ETIM	8	EC001598
ETIM	7	EC001598

Approvals / Certificates

General Product Approval



EG-Konf.



[Manufacturer Declaration](#)



RCM



For use in hazardous locations



UL

[FM](#)

[CCC-Ex](#)



ATEX



IECEx

[Miscellaneous](#)

For use in hazardous locations

Maritime application

[Type Examination Certificate](#)



ABS



BUREAU
VERITAS



DNV



LRS

[NK / Nippon Kaiji Kyokai](#)

Maritime application



RINA



RMRS

[CCS \(China Classification Society\)](#)

last modified:

10/23/2025