

M8 connector for ET connection, 4-pole, shielded



General information			
Product type designation		Connection plug	
Product description		M8 plug connector with high degree of protection, 4-pin, metal version	
Suitability for use		for connecting ET-CONNECTION nodes (e.g. SIMATIC ET 200AL) in degree of protection IP65 / 67	
Degree and class of protection			
IP degree of protection		IP65/67	
Ambient conditions			
Ambient temperature during assembly, min.		-30 °C	
Ambient temperature during assembly, max.		80 °C	
Ambient temperature during storage/transportation			
• min.		-40 °C	
• max.		80 °C	
Mechanics/material			
Outgoing feeder type		180° cable outlet	
Material of housing		metal	
Dimensions			
Width		14 mm	
Depth		47 mm	
Classifications			
		Version	Classification
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03
Approvals / Certificates			
General Product Approval			

[Manufacturer Declaration](#)

[China RoHS](#)



last modified:

4/25/2025 