

SIMATIC DP, Connection module for PROFINET interface module, ET 200 PRO, connection 2xSCRJ FO 2x push-pull plug-in connectors for PROFINET PN



Figure similar

Input current			
from supply voltage 1L+, max.		16 A; No current consumption, only infeed current, max. 16 A with derating	
from load voltage 2L+ (without load), max.		16 A; No current consumption, only infeed current, max. 16 A with derating	
Accessories			
Function description		IM PN, 2x SCRJ FO, 2x PushPull interface module	
belongs to product		IM154-4 PN HF	
Dimensions			
Width		90 mm	
Height		130 mm	
Depth		51 mm	
Weights			
Weight, approx.		325 g	
Classifications			
		Version	Classification
	eClass	14	27-24-26-03
	eClass	12	27-24-26-03
	eClass	9.1	27-24-26-03
	eClass	9	27-24-26-03
	eClass	8	27-24-26-03
	eClass	7.1	27-24-26-03
	eClass	6	27-24-26-03
	ETIM	10	EC001598
	ETIM	9	EC001598
	ETIM	8	EC001598
	ETIM	7	EC001598
	IDEA	4	3560
	UNSPSC	15	32-15-17-04

Approvals / Certificates	
General Product Approval	



EG-Konf.

[China RoHS](#)

[Miscellaneous](#)

[Manufacturer Declaration](#)





UL

General Product Approval	Maritime application
--------------------------	----------------------



Maritime application

[NK / Nippon Kaiji Ky-
okai](#)



[CCS \(China Classifica-
tion Society\)](#)



last modified:

4/7/2025 