



REPLACEMENT NF LINE BASE 30A HD, 60A GD 30A, NON-FUSED

General technical data

fastening method 2 OR 3 POINT MOUNTING HOLES

Electricity

voltage between phase and Ground (GND) rated value 240 V

voltage between phase and phase rated value 600 V

Model

product brand name SIEMENS

product type designation ENCLOSED/SAFETY SWITCH

General product approval

certificate of suitability UL

last modified:

10/22/2025 

