



REPLACEMENT NF LINE BASE 200A HD AND GD 200A, NON-FUSED

General technical data	
fastening method	2 OR 3 POINT MOUNTING HOLES
Electricity	
voltage between phase and Ground (GND) rated value	240 V
voltage between phase and phase rated value	600 V
Model	
product brand name	SIEMENS
product type designation	ENCLOSED/SAFETY SWITCH
General product approval	
certificate of suitability	UL

last modified:

10/22/2025 

