



Figure similar

SIMATIC DP, Connection module for Ethernet/IP head assembly ET 200 PRO; M12/7/8", 2x M12 and 2x 7/8"

Input current	
from supply voltage 1L+, max.	No current input, only infeed current, max. 8 A
from load voltage 2L+ (without load), max.	No current input, only infeed current, max. 8 A
Accessories	
Function description	IM PN; 2x M12 2x 7/8" interface module, power supply from 1L+ and 2L+ max. per 8 A, internal transfer 2L+ max. 8 A, 1L+ max. 5 A
belongs to product	M154-4PN High Feature
Dimensions	
Width	90 mm
Height	130 mm
Depth	51 mm
Weights	
Weight, approx.	540 g
Classifications	

	Version	Classification
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates
General Product Approval



