




Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 0.063 /0.19;
Upri(V): 500+/-5%; Usec(V): 230; Isec(A): 0.27; F(Hz): 50...60;
vector group/shielding winding: II0 /0; temperature rise/insulation
class: 40 /B; IP00; connection: screw/flat-type connection;
mounting: screws / DIN rail; EN 61558-2-1, -2-2, -2-4 >UL/CSA-
recognized< >control transformer< >isolation transformer<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	63
efficiency		0.85
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	190
relative short-circuit voltage	%	8.4
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	525
• _2 rated value	V	500
• _3 rated value	V	475
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	230
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP00
Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals

fastening method		screws / DIN rail
construction form of the iron core		EI 84/28
width	m	0.086
height	m	0.098
depth	m	0.09

Certificates/ approvals

General Product Approval	Environment
--------------------------	-------------



[Environmental Conformations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM3242-5FT10-0FA0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM3242-5FT10-0FA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM3242-5FT10-0FA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM3242-5FT10-0FA0&lang=en

last modified:

4/2/2025