



SIMATIC ET 200SP, 5 BU covers, 15 mm. for protection of empty slots

General information

Product type designation	BU cover
--------------------------	----------

Ambient conditions

Ambient temperature during operation

• min.	-40 °C
• max.	70 °C

Altitude during operation relating to sea level

• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
---	--

Dimensions

Width	15 mm
Height	73 mm
Depth	35.3 mm

Classifications

	Version	Classification
eClass	14	27-24-26-92
eClass	12	27-24-26-92
eClass	9.1	27-24-26-92
eClass	9	27-24-26-92
eClass	8	27-24-26-92
eClass	7.1	27-24-26-92
eClass	6	27-24-26-92
ETIM	10	EC002584
ETIM	9	EC002584
ETIM	8	EC002584
ETIM	7	EC002584
IDEA	4	3552
UNSPSC	15	32-15-17-03

Approvals / Certificates

General Product Approval	Railway
--------------------------	---------

[China RoHS](#)

[Miscellaneous](#)

[Manufacturer Declaration](#)



[Confirmation](#)

last modified:

5/22/2024

