

## Data sheet for Smart Access Module

Article No. : 6SL3255-0VA00-5AA0

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :



Figure similar

### Electrical data

Operating voltage (DC) 24 V

### Rated data

Operating frequency 2,400.0 ... 2,483.5 MHz

Damping factor per length (2.4 GHz), max. 17 dB/m

### Mechanical data

Degree of protection IP20 / UL open type

Net weight 28 g (0.99 oz)

### Communication

Wi-fi compatible Yes

IEEE 802.11b Yes

IEEE 802.11g Yes

### Ambient conditions

Ambient temperature during

Operation 0 ... 50 °C (32 ... 122 °F)

Storage -40 ... 70 °C (-40 ... 158 °F)

Transport -40 ... 70 °C (-40 ... 158 °F)

Relative humidity

without condensation 95 %

### Standards

Compliance with standards CE / FCC / SRRC / WPC / TRA / CNC