



incandescent lamp, clear, rated voltage 12 V AC/DC, 1.0 W, Wedge base W2 x 4.6 d,

Figure similar

| General technical data                                     |    |                   |
|--|----|-------------------|
| product designation  |    | incandescent lamp |
| type of light source                                       |    | filament lamp     |
| color of the light source                                  |    | clear             |
| socket design  |    | W2 x 4.6d         |
| product component  |    |                   |
| • series resistor  |    | No                |
| • diode  |    | No                |
| • lamp transformer   |    | No                |
| • light source   |    | Yes               |
| type of voltage of the operating voltage for actuation     |    | AC/DC             |
| operating voltage  |    |                   |
| • at AC  |    |                   |
| — at 50 Hz rated value                                     | V  | 12                |
| — at 60 Hz rated value                                     | V  | 12                |
| • at DC rated value  | V  | 12                |
| relative positive tolerance of the operating voltage       | %  | 10                |
| relative negative tolerance of the operating voltage       | %  | -15               |
| consumed current for rated value of supply voltage maximum | mA | 75                |
| type of electrical connection                              |    | Miscellaneous     |
| fastening method   |    | miscellaneous     |

| Certificates/ approvals  |                   |       |
|--------------------------|-------------------|-------|
| General Product Approval | Test Certificates | other |



[Miscellaneous](#)

[Confirmation](#)

|       |             |
|-------|-------------|
| other | Environment |
|-------|-------------|



[Environmental Confirmations](#)

Further information

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information for data generation and storage**

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2908-1AB>

**Cax online generator**

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2908-1AB>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2908-1AB>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SB2908-1AB&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2908-1AB&lang=en)

---

last modified:

4/2/2025 