

spare key PRO, safety, type 14 for keyswitch PRO Safety, scope of supply: 6 spare keys

General information		
Product type designation	Spare key	
Standards, approvals, certificates		
CE mark	No; No CE marking obligation	
Ambient conditions		
Ambient temperature during operation		
• min.	-40 °C	
• max.	80 °C	
Ambient temperature during storage/transportation		
• min.	-40 °C	
• max.	80 °C	
Relative humidity		
• Operation, max.	90 %	
Mechanics/material		
Material		
• Sheet metal	Yes	
Dimensions		
Width	15 mm; Approximate dimension	
Height	35 mm; Approximate dimension	
Thickness	4 mm	
Weights		
Weight (without packaging)	5 g	
Scope of supply		
Delivery quantity in pieces	6; 3 pairs	
Other		
Merchandise	Yes; RAFI 9.30.275.011/0000	
Manufacturer name	RAFI GmbH & Co.KG	
Manufacturer's address	Ravensburger Str. 128-134, 88276 Berg, Germany	
Target devices	6AV7674-1ME50-0AA0	
Classifications		
	Version	Classification
eClass	14	27-33-02-92
eClass	12	27-33-02-92
eClass	9.1	27-33-02-92
eClass	9	27-33-02-92
eClass	8	27-24-92-03
eClass	7.1	27-24-92-03
eClass	6	27-24-92-03
ETIM	10	EC002584
ETIM	9	EC002584
ETIM	8	EC002584
ETIM	7	EC002584
IDEA	4	3552
UNSPSC	15	32-15-17-03
Further information		

Usable in the following products: Detailed information can be found in the cross-list, which is available for download in the following SIOS note: 40466415

last modified:

2/16/2026 