



SIMATIC cable grip for SIMATIC BusAdapter, 5 units

General information			
Product type designation		Strain relief for PROFINET	
Ambient conditions			
Ambient temperature during operation			
• min.		0 °C	
• max.		60 °C	
Absolute humidity			
• dew point, min.		-60 °C; suitable for dry room applications	
Dimensions			
Width		15.5 mm	
Height		51.4 mm	
Depth		45 mm	
Width of cable tie, rec.		2.5 mm	
Width of cable tie, max.		7 mm	
Length of cable tie, min.		60 mm	
Classifications			
		Version	Classification
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03
	Approvals / Certificates		
General Product Approval			

[Manufacturer Declaration](#)

