



SIMATIC ET 200SP, set for 5 shield connections, with 5 shield terminals, 5 shield supports, 5 support elements

General information																																					
Product type designation	Shield connection																																				
Installation type/mounting																																					
Mounting	can be plugged into ET 200SP BaseUnit																																				
Ambient conditions																																					
Ambient temperature during operation																																					
• min.	-40 °C																																				
• max.	70 °C																																				
Altitude during operation relating to sea level																																					
• Installation altitude above sea level, max.	5 000 m																																				
Absolute humidity																																					
• dew point, min.	-60 °C; suitable for dry room applications																																				
Mechanics/material																																					
Material	Brass, nickel-plated																																				
Dimensions																																					
Width	15 mm																																				
Height	14 mm																																				
Depth	80 mm																																				
Classifications																																					
	<table border="1"> <thead> <tr> <th></th> <th>Version</th> <th>Classification</th> </tr> </thead> <tbody> <tr> <td>eClass</td> <td>14</td> <td>27-24-26-92</td> </tr> <tr> <td>eClass</td> <td>12</td> <td>27-24-26-92</td> </tr> <tr> <td>eClass</td> <td>9.1</td> <td>27-24-26-92</td> </tr> <tr> <td>eClass</td> <td>9</td> <td>27-24-26-92</td> </tr> <tr> <td>eClass</td> <td>8</td> <td>27-24-26-92</td> </tr> <tr> <td>eClass</td> <td>7.1</td> <td>27-24-26-92</td> </tr> <tr> <td>eClass</td> <td>6</td> <td>27-24-26-92</td> </tr> <tr> <td>ETIM</td> <td>10</td> <td>EC002584</td> </tr> <tr> <td>ETIM</td> <td>9</td> <td>EC002584</td> </tr> <tr> <td>ETIM</td> <td>8</td> <td>EC002584</td> </tr> <tr> <td>ETIM</td> <td>7</td> <td>EC002584</td> </tr> </tbody> </table>		Version	Classification	eClass	14	27-24-26-92	eClass	12	27-24-26-92	eClass	9.1	27-24-26-92	eClass	9	27-24-26-92	eClass	8	27-24-26-92	eClass	7.1	27-24-26-92	eClass	6	27-24-26-92	ETIM	10	EC002584	ETIM	9	EC002584	ETIM	8	EC002584	ETIM	7	EC002584
	Version	Classification																																			
eClass	14	27-24-26-92																																			
eClass	12	27-24-26-92																																			
eClass	9.1	27-24-26-92																																			
eClass	9	27-24-26-92																																			
eClass	8	27-24-26-92																																			
eClass	7.1	27-24-26-92																																			
eClass	6	27-24-26-92																																			
ETIM	10	EC002584																																			
ETIM	9	EC002584																																			
ETIM	8	EC002584																																			
ETIM	7	EC002584																																			
Approvals / Certificates																																					
General Product Approval																																					



---

last modified:

2/1/2026 