



30mm Command/52, Chrome Finish Heavy Duty, Watertight/Oiltight Complete Metal Unit Illuminated Push-Pull Operator Full Voltage, 120V AC/DC LED Lamp Mushroom Head Cap Small 1 3/4" (44.5 mm) Metal, Chrome with Red Lens 2 Position Maintained, Pull-to-Release with 1 N.O. - 1 N.C. Heavy Duty Contacts, A600/P600 UL Listed, CSA Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards

| Enclosure | |
|---|---------------------------|
| number of command points | 1 |
| delivery state as a kit | No |
| Actuator | |
| product extension optional light source | Yes |
| number of contact modules | 1 |
| type of unlocking device | pull-to-unlatch mechanism |
| number of switching positions | 2 |
| Front ring | |
| product component front ring | Yes |
| design of the front ring | standard |
| material of the front ring | metal |
| Contact block/ lampholder | |
| number of lampholders | 1 |
| Display | |
| number of LED modules | 1 |
| General technical data | |
| product function positive opening | Yes |
| product component | |
| • lamp transformer | No |
| • light source | Yes |
| insulation voltage rated value | 600 V |
| type of voltage | |
| • of the operating voltage | AC/DC |
| • of the input voltage | AC/DC |
| surge voltage resistance rated value | 4 kV |
| protection class IP | IP66 |
| protection class IP of the terminal | IP20 |
| thermal current | 10 A |
| Net Weight | 0.23 kg |
| Supply voltage | |
| type of voltage of the supply voltage of the light source | AC/DC |
| supply voltage of the light source at AC at 60 Hz rated value | |
| • | 120 V |
| supply voltage of the light source at DC rated value | |
| • | 120 V |
| Auxiliary circuit | |
| number of NC contacts for auxiliary contacts | 1 |
| number of NO contacts for auxiliary contacts | 1 |

| | |
|---|----------------|
| operational current at AC-15 | |
| • at 110 V rated value | 60 A |
| • at 230 V rated value | 30 A |
| • at 400 V rated value | 15 A |
| • at 500 V rated value | 12 A |
| Connections/ Terminals | |
| type of electrical connection | screw terminal |
| tightening torque of the screws in the bracket maximum | 20 N·m |
| tightening torque [lbf·in] with screw-type terminals | 8 lbf·in |
| Lamp | |
| color of the light source | red |
| Ambient conditions | |
| ambient temperature | |
| • during operation | -35 ... +70 °C |
| • during storage | -40 ... +85 °C |
| Installation/ mounting/ dimensions | |
| shape of the installation opening | round |
| Further information | |

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52PP2E2AB>
Cax online generator
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52PP2E2AB>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/US2:52PP2E2AB>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52PP2E2AB&lang=en

last modified:

10/23/2025 