

Selector switch, metal Maintained Long lever, G Cam 3 position Operator only white insert Non-Illuminated UL file E22655 in Vol. 6 (7) Sec. 13 (2)

design of the product	Actuator round
Enclosure	
number of command points	1
delivery state as a kit	No
Actuator	
design of the actuating element	selector switch
material of the actuating element	plastic
shape of the actuating element	Extended handle
type of unlocking device	rotate-to-unlatch mechanism
number of switching positions	3
Front ring	
product component front ring	Yes
design of the front ring	standard
material of the front ring	metal
color of the front ring	chrome
Holder	
material of the holder	Metal
General technical data	
product component	
• light source	No
degree of pollution	1
protection class IP	IP66
operating frequency maximum	600 1/h
Net Weight	0.12 kg
Ambient conditions	
ambient temperature	
• during operation	-35 ... +70 °C
• during storage	-40 ... +85 °C
Installation/ mounting/ dimensions	
shape of the installation opening	round
Further information	
Information on the packaging	
https://support.industry.siemens.com/cs/ww/en/view/109813875	
Information for data generation and storage	
https://support.industry.siemens.com/cs/ww/en/view/109995012	
Information- and Downloadcenter (Catalogs, Brochures,...)	
https://www.siemens.com/ic10	
Industry Mall (Online ordering system)	
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52SB2GAB	
Cax online generator	
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52SB2GAB	
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)	
https://support.industry.siemens.com/cs/ww/en/ps/US2:52SB2GAB	
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)	
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52SB2GAB&lang=en	

last modified:

10/23/2025 