

Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. Type: OEM DISCONNECT Std: UL V. Rating: 600V A. Rating: 60A Number of poles: 3P F. Rating: 60Hz Action: SINGLE THROW Material: 304SS Enclosure: TYPE 3R/12. 2-3 point mounting holes. Insulation: YES O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: OUTDOOR/INDUSTRIAL

General technical data	
fastening method	2 OR 3 POINT MOUNTING HOLES
Electricity	
voltage between phase and phase rated value	600 V
Model	
product brand name	Siemens
product type designation	OEM DISCONNECT
Mechanical Design	
material	304SS
General product approval	
certificate of suitability	UL
degree of protection NEMA rating	TYPE 3R/12

last modified:

10/23/2025 

