



Figure similar

SIMATIC DP, Connection module for Ethernet/IP head assembly ET 200 PRO; M12/7/8", 2x M12 and 2x 7/8"

Input current																																											
from supply voltage 1L+, max.	No current input, only infeed current, max. 8 A																																										
from load voltage 2L+ (without load), max.	No current input, only infeed current, max. 8 A																																										
Accessories																																											
Function description	IM PN; 2x M12 2x 7/8" interface module, power supply from 1L+ and 2L+ max. per 8 A, internal transfer 2L+ max. 8 A, 1L+ max. 5 A																																										
belongs to product	M154-4PN High Feature																																										
Dimensions																																											
Width	90 mm																																										
Height	130 mm																																										
Depth	51 mm																																										
Weights																																											
Weight, approx.	540 g																																										
Classifications																																											
	<table border="1"> <thead> <tr> <th></th> <th>Version</th> <th>Classification</th> </tr> </thead> <tbody> <tr> <td>eClass</td> <td>14</td> <td>27-24-26-03</td> </tr> <tr> <td>eClass</td> <td>12</td> <td>27-24-26-03</td> </tr> <tr> <td>eClass</td> <td>9.1</td> <td>27-24-26-03</td> </tr> <tr> <td>eClass</td> <td>9</td> <td>27-24-26-03</td> </tr> <tr> <td>eClass</td> <td>8</td> <td>27-24-26-03</td> </tr> <tr> <td>eClass</td> <td>7.1</td> <td>27-24-26-03</td> </tr> <tr> <td>eClass</td> <td>6</td> <td>27-24-26-03</td> </tr> <tr> <td>ETIM</td> <td>10</td> <td>EC001598</td> </tr> <tr> <td>ETIM</td> <td>9</td> <td>EC001598</td> </tr> <tr> <td>ETIM</td> <td>8</td> <td>EC001598</td> </tr> <tr> <td>ETIM</td> <td>7</td> <td>EC001598</td> </tr> <tr> <td>IDEA</td> <td>4</td> <td>3560</td> </tr> <tr> <td>UNSPSC</td> <td>15</td> <td>32-15-17-04</td> </tr> </tbody> </table>		Version	Classification	eClass	14	27-24-26-03	eClass	12	27-24-26-03	eClass	9.1	27-24-26-03	eClass	9	27-24-26-03	eClass	8	27-24-26-03	eClass	7.1	27-24-26-03	eClass	6	27-24-26-03	ETIM	10	EC001598	ETIM	9	EC001598	ETIM	8	EC001598	ETIM	7	EC001598	IDEA	4	3560	UNSPSC	15	32-15-17-04
	Version	Classification																																									
eClass	14	27-24-26-03																																									
eClass	12	27-24-26-03																																									
eClass	9.1	27-24-26-03																																									
eClass	9	27-24-26-03																																									
eClass	8	27-24-26-03																																									
eClass	7.1	27-24-26-03																																									
eClass	6	27-24-26-03																																									
ETIM	10	EC001598																																									
ETIM	9	EC001598																																									
ETIM	8	EC001598																																									
ETIM	7	EC001598																																									
IDEA	4	3560																																									
UNSPSC	15	32-15-17-04																																									
Approvals / Certificates																																											
General Product Approval																																											



