

AS-Interface M12 branch U_ASI and Uaux, 1 m cable with M12 cable socket angled IP67/68/69K, max. 4 A



product category	AS-Interface accessories
product designation	AS-i flat cable transition to M12
suitability for use	AS-i flat cable (yellow) and AUX flat cable (black) connections
General technical data	
operating voltage according to AS-Interface specification	26.5 ... 31.6 V
operational current rated value	3 A
number of poles	4
contact rating maximum	4 A
protection class IP	IP67, IP68, IP69K
Substance Prohibittance (day/month/year)	07/01/2006
Net Weight	0.077 kg
Installation/ mounting/ dimensions	
mounting type	screw mounting on the lower part of enclosure
tightening torque of fixing screw minimum	1.65 N·m
tightening torque of fixing screw maximum	1.65 N·m
height	22 mm
width	27.7 mm
length	40.5 mm
Ambient conditions	
ambient temperature	
• during operation	-25 ... +75 °C
• during storage	-25 ... +85 °C
Connections/ Terminals	
type of electrical connection	insulation piercing method for AS-Interface flat cable
feeder type	round cable with M12 socket, A-coding
mounting type of the flat cable	hinged cover with stainless steel bolt
installation or assembly note	flat cable end not permitted in the branch
contact assignment of the M12 connection	
• at pin 1	ASI+
• at pin 2	not connected
• at pin 3	ASI-
• at pin 4	AUX+
• at pin 5	not connected
length of the round cable	1 m
connectable conductor cross-section of the round cable	0.34 mm ²
Approvals Certificates	
Environment	General Product Approval
	EMV

