



AS-i compact module K20 digital A/B slave, 4 DI/4 DQ, IP67 4 x input, maximum 200 mA 4 x output, 1 A, 24 V DC maximal 2 A for all outputs 8 x M8 sockets

General technical data	
design of the product	digital I/O modules for operation in the field, IP67 - K20
design of the device type	A/B slave (Spec. 3.0)
type of electrical connection of the inputs and outputs	M8 screw-type terminals
Sensor supply	
type of voltage supply for sensor supply	using AS-Interface
input voltage	16.5 ... 30 V
property of the sensor supply short-circuit and overload resistant	Yes
ampacity of the sensor supply for all inputs	
• at ambient temperature 40 °C	200 mA
• at ambient temperature 55 °C	150 mA
Inputs	
number of digital inputs	4
type of connection technology	2- and 3-wire technology
type of voltage of the input voltages	DC
input current at digital input	
• for signal <1> minimum	6 mA
• with signal <0> maximum	1.5 mA
design of the pin assignment of the inputs	standard assignment
Outputs	
number of digital outputs	4
type of voltage of output voltages	DC
ampacity of the semiconductor output at DC-13 at 24 V	1 A
type of switching output	PNP transistor
design of the pin assignment of the outputs	standard assignment
property of the output short-circuit proof	Yes
Ambient conditions	
ambient temperature	
• during operation	-25 ... +70 °C
• during storage	-40 ... +85 °C
protection class IP	IP67
Mechanical data	
width	20 mm
height	164 mm
depth	45 mm
fastening method	no mounting plate required
shock resistance	15 g / 11 ms
Certificates/ approvals	

General Product Approval	EMV
--------------------------	-----



Test Certificates	Maritime application	other
-------------------	----------------------	-------

[Special Test Certificate](#)



[Miscellaneous](#)

[Confirmation](#)

other	Environment	Industrial Communication
-------	-------------	--------------------------



[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK2400-1CT30-0AA3>

Cax online generator



<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK2400-1CT30-0AA3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK2400-1CT30-0AA3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK2400-1CT30-0AA3&lang=en



last modified:

4/4/2026 