



Electronic remote reset 220...250 V AC/DC for 3RU Size S00...S3

product brand name	SIRIUS
product category	Reset modules
product designation	Electric reset
design of the product	Electrical Remote RESET
product type designation	3RU19
<b>General technical data</b>	
size of overload relay	S00, S0, S2, S3
apparent power consumption at AC at 50/60 Hz maximum	80 VA
consumed active power at DC maximum	70 W
operating frequency maximum	60 1/h
ON period/maximum	
• minimum	0.2 ms
• maximum	4 s
Substance Prohibittance (day/month/year)	07/01/2006
Net Weight	0.056 g
type of voltage of the control supply voltage	AC/DC
control supply voltage 1 at AC	
• at 50 Hz	220 ... 250 V
• at 60 Hz	220 ... 250 V
control supply voltage frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
control supply voltage 1 at DC	220 ... 250 V
<b>Ambient conditions</b>	
ambient temperature	
• during operation	-20 ... +70 °C
• during storage	-50 ... +80 °C
<b>Connections/ Terminals</b>	
type of electrical connection for auxiliary and control circuit	screw-type terminals
connectable conductor cross-section for auxiliary contacts	
• solid or stranded	0.5 ... 2.5 mm <sup>2</sup>
• finely stranded with core end processing	0.5 ... 2.5 mm <sup>2</sup>
type of connectable conductor cross-sections for auxiliary contacts	
• solid	2x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.75 ... 2.5 mm <sup>2</sup> )
• finely stranded with core end processing	2x (0.5 ... 1.5 mm <sup>2</sup> ), 2x (0.75 ... 2.5 mm <sup>2</sup> )
<b>Approvals Certificates</b>	
Environment	General Product Approval
	Test Certificates

[Environmental Con-  
firmations](#)



[Type Test Certific-  
ates/Test Report](#)

Test Certificates	Maritime application	other
-------------------	----------------------	-------

[Special Test Certific-  
ate](#)



[Confirmation](#)

other	Railway
-------	---------



[Special Test Certific-  
ate](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RU1900-2AM71>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RU1900-2AM71>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RU1900-2AM71>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RU1900-2AM71&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RU1900-2AM71&lang=en)



