



incandescent lamp, clear, rated voltage 30 V AC/DC, 1.0 W, Wedge base W2 x 4.6 d,

Figure similar

General technical data		
product designation		incandescent lamp
type of light source		filament lamp
color of the light source		clear
socket design		W2 x 4.6d
product component		
• series resistor		No
• diode		No
• lamp transformer		No
• light source		Yes
type of voltage of the operating voltage for actuation		AC/DC
operating voltage		
• at AC		
— at 50 Hz rated value	V	28 ... 30
— at 60 Hz rated value	V	28 ... 30
• at DC rated value	V	28 ... 30
consumed current for rated value of supply voltage maximum	mA	50
type of electrical connection		Miscellaneous
fastening method		miscellaneous

Certificates/ approvals		
General Product Approval	Test Certificates	other



[Miscellaneous](#)

[Confirmation](#)

other	Environment
-------	-------------



[Environmental Confirmations](#)

### Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
 Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SB2908-1AD>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SB2908-1AD>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SB2908-1AD>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[https://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SB2908-1AD&lang=en](https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SB2908-1AD&lang=en)

---

last modified:

4/2/2025 