

circular conduc. terminal TA1.1 10...95 mm² with auxiliary conductor voltage tap 4 units accessory for: 3VA10/11



Model	
product brand name	SETRON
product designation	Circular conductor terminal voltage tap 4 units
design of the product	Connection method
accessories	Wire connector
General technical data	
designation / of the terminal	TA1.1
type of electrical connection / with control wire tap	Yes
Mechanical Design	
Net Weight	76 g
Connections according IEC	
connectable conductor cross-section	
• for copper cable / stranded / minimum	10 mm ²
• for copper cable / stranded / maximum	95 mm ²
• for aluminum cable / stranded / minimum	10 mm ²
• for aluminum cable / stranded / maximum	95 mm ²
stripped length	12,2 mm
tightening torque / when using copper cables	
• solid	10mm ² : 6.2 Nm, 16mm ² : 11.3 Nm
• stranded	10mm ² : 6.2 Nm, 16 - 95 mm ² : 11.3 Nm
• finely stranded	10mm ² : 6.2 Nm, 16 - 35mm ² : 11.3 Nm
• finely stranded / with core end processing	10 - 16 mm ² : 6.2 Nm, 25 - 50 mm ² : 7.9 Nm, 70 mm ² : 11.3 Nm
Connetctions according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C
stripped length	0.48 in
connectable conductor cross-section	
• for copper cable / stranded / minimum	8 AWG
• for copper cable / stranded / maximum	3/0 AWG
• for aluminum cable / stranded / minimum	8 AWG
• for aluminum cable / stranded / maximum	3/0 AWG
tightening torque / when using copper cables	
• stranded	8 AWG: 55 lb-in, 6-3/0 AWG: 100 lb-in
Certificates	
General Product Approval	EMV

[Miscellaneous](#)



[Confirmation](#)



Test Certificates	Maritime application	other	Environment		
-------------------	----------------------	-------	-------------	--	--

[Type Test Certificates/Test Report](#)



[Miscellaneous](#)

[Confirmation](#)

[Environmental Confirmations](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9114-0JG11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9114-0JG11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



https://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9114-0JG11

CAX-Online-Generator

<https://www.siemens.com/cax>

Tender specifications

<https://www.siemens.com/specifications>



last modified:

4/6/2026

