



Figure similar

TRANSFORMER SITAS; PHASES:1; PN/PN(S6)(KVA):0,1 /0,31;
UPRI(V):550-525-500-480-460- 440-415-400-380-230-208;
USEC(V):48-(2X24); ISEC(A):2,08-4,2; F(HZ):50...60; VECTOR
GR./SHIELD WNG.:II0 /0; TA/ISOKL:40 /B; IP00; TYPE OF
TERMINALS:SCREW/TAB CONNECTION;
INSTALLATION:SCREWS/MOUNTING RAILS; EN 61558-2-2, -2-6
>UL/CSA-RECOGNIZED< >CONTROL CIRCUIT
TRANSFORMER< >SAFETY ISOLATING TRANSFORMER<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	100
efficiency		0.86
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	310
relative short-circuit voltage	%	10
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	550
• _2 rated value	V	525
• _3 rated value	V	500
• _4 rated value	V	480
• _5 rated value	V	460
• _6 rated value	V	440
• _7 rated value	V	415
• _8 rated value	V	400
• _9 rated value	V	380
• _10 rated value	V	230
• _11 rated value	V	208
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50
Ambient conditions		
thermal class according to IEC 60085		B

ambient temperature rated value	°C	40
protection class IP		IP00
Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals
fastening method		screws / DIN rail
construction form of the iron core		EI 84/42
width	m	0.086
height	m	0.098
depth	m	0.102
Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM3442-8DB40-0FA0>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM3442-8DB40-0FA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AM3442-8DB40-0FA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM3442-8DB40-0FA0&lang=en

last modified:

4/23/2025