



Figure similar

CURRENT SUPPLY (UNSCREENED); PHASES:3; PN(KW):1,92; UPRI(V):500-400(415); USEC(V DC):24; ISEC(A DC):80/96 (60/40 CEL); F(HZ):50...60; VECTOR GR./SHIELD WNG.:II0 /0; PROTECTION CL.:I; TA/ISOKL:60 /B; W(%):4,2; IP00; TYPE OF TERMINALS:SCREW CONNECTION; INSTALLATION:SCREW; EN 61558-2-6, EN61131-2 >SAFETY ISOLATING TRANSFORMER<

General technical data		
product designation		4AV3601-2EB00-0A
product brand name		SIDAC
vector group		II0
certificate of suitability		CE
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
• varistor protective wiring		Yes
operating resource protection class		I
number of shielding windings		0
Inputs		
phase number of the inputs		3
type of current of the inputs		AC
input voltage		
• _1 rated value	V	500
• _2 rated value	V	400
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
input voltage		
• minimum	V	360
• maximum	V	530
type of electrical connection at input for main current circuit		screw-type terminals
Outputs		
type of current		
• _1 at output		DC
output voltage		
• _1 rated value	V	24
output voltage of the measurement signal at analog output at DC maximum	V	28.8
output voltage of the measurement signal at analog output at DC minimum	V	20.4
output current		
• _1 rated value	A	80
type of electrical connection at output for main current circuit		screw-type terminals

relative residual ripple		
of the output voltage 1 for main current circuit maximum	%	5
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	60
protection class IP		IP00
Mechanical data		
fastening method		screws
construction form of the iron core		3UI 132/70
width	mm	295
height	mm	255
depth	mm	290
Certificates/ approvals		
General Product Approval	other	Environment



[Confirmation](#)

[Confirmation](#)



[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information for data generation and storage

<https://support.industry.siemens.com/cs/ww/en/view/109995012>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AV3601-2EB00-0A>

Cax online generator

<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AV3601-2EB00-0A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4AV3601-2EB00-0A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AV3601-2EB00-0A&lang=en

last modified:

6/27/2025