

SIMATIC ET 200SP, BaseUnit BU-SEND, for station expansion of ET 200SP via ET connection, WxH: 20 mmx117 mm

General information	
HW functional status	from FS04
Hardware configuration	
Slots	
• Number of slots	1
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	2 000 m; On request: Installation altitudes greater than 2 000 m
Absolute humidity	
• dew point, min.	-60 °C; suitable for dry room applications
Dimensions	
Width	20 mm
Height	117 mm
Depth	35 mm
Weights	
Weight, approx.	30 g
Classifications	

	Version	Classification
eClass	16	27-24-26-03
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates
General Product Approval



[Manufacturer Declaration](#)



General Product Approval	For use in hazardous locations
--------------------------	--------------------------------



[CCC-Ex](#)

[FM](#)



For use in hazardous locations

Maritime application



[Type Examination Certificate](#)

[Miscellaneous](#)

[CCC-Ex](#)



last modified:

2/1/2026 