



SIMATIC ET 200SP/BL, 1000 labeling strips, light gray, 10 sheets DIN A4, perforated, paper, 180 g/m2

General information			
Product type designation		Labeling strips, paper	
Ambient conditions			
Ambient temperature during operation			
• min.		0 °C	
• max.		60 °C	
Absolute humidity			
• dew point, min.		-60 °C; suitable for dry room applications	
Mechanics/material			
Color		light gray	
Dimensions			
Width		13 mm	
Height		31 mm	
Scope of supply			
Delivery quantity in pieces		1	
Components included		1 000; 10 units, DIN A4 sheets with 100 labeling strips each	
• Number of individual strips			
Classifications			
		Version	Classification
	eClass	16	27-24-26-92
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03
Approvals / Certificates			
General Product Approval			Maritime application

[Manufacturer Declaration](#)

[Miscellaneous](#)



[China RoHS](#)

[Manufacturer Declaration](#)



last modified:

2/1/2026