



SIMATIC ET 200SP/BL, 500 labeling strips, light gray, roll with 500 strips

General information	
Product type designation	Labeling strips, foil
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	60 °C
Absolute humidity	
• dew point, min.	-60 °C; suitable for dry room applications
Mechanics/material	
Color	light gray
Dimensions	
Width	13 mm
Height	31 mm
Outer diameter of the thermal printer roll	70 mm
Inner diameter of roll	40 mm
Width of the thermal printer roll	62 mm
Scope of supply	
Delivery quantity in pieces	1
Components included	
• Number of individual strips	500; Individual labels per role
Classifications	

	Version	Classification
eClass	16	27-24-26-92
eClass	14	27-24-26-92
eClass	12	27-24-26-92
eClass	9.1	27-24-26-92
eClass	9	27-24-26-92
eClass	8	27-24-26-92
eClass	7.1	27-24-26-92
eClass	6	27-24-26-92
ETIM	10	EC002584
ETIM	9	EC002584
ETIM	8	EC002584
ETIM	7	EC002584
IDEA	4	3552
UNSPSC	15	32-15-17-03

[Manufacturer Declaration](#)



last modified:

2/1/2026 