



SIMATIC ET 200SP, set for 5 shield connections, with 5 shield terminals, 5 shield supports, 5 support elements

General information			
Product type designation	Shield connection		
Installation type/mounting			
Mounting	can be plugged into ET 200SP BaseUnit		
Ambient conditions			
Ambient temperature during operation			
• min.	-40 °C		
• max.	70 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m		
Absolute humidity			
• dew point, min.	-60 °C; suitable for dry room applications		
Mechanics/material			
Material	Brass, nickel-plated		
Dimensions			
Width	15 mm		
Height	14 mm		
Depth	80 mm		
Classifications			
		Version	Classification
	eClass	16	27-24-26-92
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
ETIM	7	EC002584	
Approvals / Certificates			
General Product Approval			



last modified:

2/1/2026 