

SIMATIC DP, Connection module for PROFINET interface module, ET 200 PRO, connection 2xSCRJ FO 2x push-pull plug-in connectors for PROFINET PN



Figure similar

Input current	
from supply voltage 1L+, max.	16 A; No current consumption, only infeed current, max. 16 A with derating
from load voltage 2L+ (without load), max.	16 A; No current consumption, only infeed current, max. 16 A with derating
Accessories	
Function description	IM PN, 2x SCRJ FO, 2x PushPull interface module
belongs to product	IM154-4 PN HF
Dimensions	
Width	90 mm
Height	130 mm
Depth	51 mm
Weights	
Weight, approx.	325 g
Classifications	

	Version	Classification
eClass	16	27-24-26-03
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598
IDEA	4	3560
UNSPSC	15	32-15-17-04

Approvals / Certificates
General Product Approval

[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval

Maritime application



[China RoHS](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

[KR \(Korean Register of Shipping\)](#)

last modified:

4/7/2025