



Figure similar

SIMATIC DP, Connection module for PROFINET interface module ET 200 PRO IM154-3 PN HF, M12 7/8" S , 2x M12 and 2x 7/8"

Input current	
from supply voltage 1L+, max.	8 A; No current input, only infeed current, max. 8 A
from load voltage 2L+ (without load), max.	8 A; No current input, only infeed current, max. 8 A
Accessories	
Function description	IM PN; 2x M12 2x 7/8" interface module, power supply from 1L+ and 2L+ max. per 8 A, internal transfer 2L+ max. 8 A, 1L+ max. 5 A
belongs to product	ET 200pro; IM154-3 PN HF
Dimensions	
Width	60 mm
Height	130 mm
Depth	51 mm
Weights	
Weight, approx.	440 g

Classifications			
		Version	Classification
eClass		16	27-24-26-03
eClass		14	27-24-26-03
eClass		12	27-24-26-03
eClass		9.1	27-24-26-03
eClass		9	27-24-26-03
eClass		8	27-24-26-03
eClass		7.1	27-24-26-03
eClass		6	27-24-26-03
ETIM		10	EC001598
ETIM		9	EC001598
ETIM		8	EC001598
ETIM		7	EC001598
IDEA		4	3560
UNSPSC		15	32-15-17-04

Approvals / Certificates	
General Product Approval	



[Miscellaneous](#)[Manufacturer Declaration](#)



General Product Approval

Maritime application



[China RoHS](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

Maritime application

[KR \(Korean Register of Shipping\)](#)

last modified:

3/12/2024