



Figure similar

SIMATIC DP, Connection module for PROFINET interface module ET 200 PRO IM154-3 PN HF, M12 M12-L S, 2x M12-D and 2x M12-L

Input current	
from supply voltage 1L+, max.	12 A; No current input, only infeed current, max. 12 A
from load voltage 2L+ (without load), max.	12 A; No current input, only infeed current, max. 12 A
Accessories	
Function description	Interface module IM PN; 2x M12-D, 2x M12-L
belongs to product	ET 200pro; IM154-3 PN HF
Dimensions	
Width	60 mm
Height	130 mm
Depth	49 mm
Weights	
Weight, approx.	390 g
Classifications	

	Version	Classification
eClass	16	27-24-26-03
eClass	14	27-24-26-03
eClass	12	27-24-26-03
eClass	9.1	27-24-26-03
eClass	9	27-24-26-03
eClass	8	27-24-26-03
eClass	7.1	27-24-26-03
eClass	6	27-24-26-03
ETIM	10	EC001598
ETIM	9	EC001598
ETIM	8	EC001598
ETIM	7	EC001598

Approvals / Certificates
General Product Approval



[Miscellaneous](#)

[Manufacturer Declaration](#)



General Product Approval	Maritime application
--------------------------	----------------------



[China RoHS](#)



Maritime application



[NK / Nippon Kaiji Kyokai](#)



[CCS \(China Classification Society\)](#)

[KR \(Korean Register of Shipping\)](#)

last modified:

5/22/2024