



Figure similar

SIMATIC DP, connection plug for PROFIBUS up to 12 Mbps 90° cable outlet, 15.8x 59x 35.6 mm (WxHxD), insulation displacement method FastConnect, without PG socket 100 units 6ES7972-0BA52-0XA0 per packing unit

General information			
Product type designation	PROFIBUS connector		
Ambient conditions			
Ambient temperature during operation			
• min.	0 °C		
• max.	60 °C		
Mechanics/material			
Design of housing	plastic		
Dimensions			
Width	15.8 mm		
Height	59 mm		
Depth	35.6 mm		
Weights			
Weight, approx.	10 g		
Classifications			
		Version	Classification
	eClass	16	27-24-26-92
	eClass	14	27-24-26-92
	eClass	12	27-24-26-92
	eClass	9.1	27-24-26-92
	eClass	9	27-24-26-92
	eClass	8	27-24-26-92
	eClass	7.1	27-24-26-92
	eClass	6	27-24-26-92
	ETIM	10	EC002584
	ETIM	9	EC002584
	ETIM	8	EC002584
	ETIM	7	EC002584
	IDEA	4	3552
	UNSPSC	15	32-15-17-03
Approvals / Certificates			
General Product Approval			

[Miscellaneous](#)



[Manufacturer Declaration](#)



[China RoHS](#)

[Manufacturer Declaration](#)

For use in hazardous locations	Maritime application
--------------------------------	----------------------



[EM](#)

[EM](#)



last modified:

3/12/2024 