



SCALANCE XB116 unmanaged IE switch, 16x 10/100 Mbit/s RJ45 ports; for setting up small star and line topologies; LED diagnostics, IP20, Redundant power supply, 24 V AC/DC Manual available as a download .

product type designation	
product brand name	SCALANCE
product type designation	XB116
Technical Product Detail Page	https://i.siemens.com/1P6GK5116-0BA00-2AB2
transfer rate	
transfer rate	10, 100 Mbit/s
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	16; RJ45
interfaces / other	
number of electrical connections	
• for power supply	1
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	4.8 W
• supply voltage / 1 / voltage range	19.2 ... 28.8
• consumed current / 1 / maximum	0.2 A
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	0,6 A / 60 V
type of voltage / 2 / of the supply voltage	AC
• supply voltage / 2 / voltage range	19.2 ... 28.8
ambient conditions	
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	80 mm
height	117 mm
depth	109 mm
net weight	0.375 kg
fastening method	

• 35 mm DIN-rail mounting • wall mounting • S7-300 rail mounting • S7-1500 rail mounting	Yes No No No
product functions / management, configuration, engineering	
product function	
• multiport mirroring • CoS • switch-managed	No Yes No
PROFINET conformity class	A
product functions / redundancy	
product function	
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	Yes No
standards, specifications, approvals	
certificate of suitability	
• CE marking • cULus approval • KC approval • Regulatory Compliance Mark (RCM)	Yes Yes Yes Yes
standard	
• for EMC interference emission • for immunity to EMC • for safety / from CSA and UL	EN 61000-6-4 (Class B) 61000-6-2 UL 60950-1, CSA C22.2 No. 60950-1
standards, specifications, approvals / hazardous environments	
certificate of suitability	
• ATEX • UKEX • IECEx • ULhazloc approval • CCC / for hazardous zone according to GB standard • FM registration	Yes Yes Yes Yes Yes Yes
standards, specifications, approvals / other	
certificate of suitability	
• RoHS conformity	Yes
resistance to air pollution / conformity according to ANSI/ISA-71.04	Yes; G3
standards, specifications, approvals / Environmental Product Declaration	
Environmental Product Declaration	Yes
global warming potential [CO2 eq]	
• total • during manufacturing • during operation • after end of life	252.5 kg 26.6 kg 225.28 kg 0.6 kg
product functions / general	
MTBF	80 a
warranty period	5 a
further information / internet links	
internet link	
• to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to web page: SiePortal • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support	https://support.industry.siemens.com/cs/ww/en/view/109766358 https://www.siemens.com/tstcloud https://www.siemens.com/simatic-net https://sieportal.siemens.com/ https://www.automation.siemens.com/bilddb https://www.siemens.com/cax https://support.industry.siemens.com
security information	

security information	Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement - and continuously maintain - a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)
----------------------	---

Approvals / Certificates

Environmental Product Declaration	
• global warming potential [CO2 eq] / during manufacturing	26.6 kg
• global warming potential [CO2 eq] / during operation	225.28 kg
• global warming potential [CO2 eq] / after end of life	0.6 kg
• global warming potential [CO2 eq] / total	252.5 kg

General Product Approval



[Declaration of Con-
formity](#)



[China RoHS](#)



General Product Approval



[China RoHS](#)



For use in hazardous locations

[FM](#)

[CCC-Ex](#)

[Type Test Certific-
ates/Test Report](#)

[PROFINET](#)

last modified: 4/23/2026