

30mm BlackMax, Epoxy Coated Corrosion Resistant Complete Metal Unit
Illuminated Push-Pull Operator Full Voltage, 120V AC/DC Incandescent Lamp
Mushroom Head Cap Small 1 3/4" (44.5 mm) Plastic, Green 3 Position Momentary
1 N.C.+1 N.C. Extra Late Break Heavy Duty Contacts, A600/P600 UL Listed, CSA
Certified NEMA 1,3,3R,4,4X,12,13 & Automotive Standards



General technical data

Net Weight	0.23 kg
------------	---------

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=US2:52BP3ESU>
Cax online generator
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=US2:52BP3ESU>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/US2:52BP3ESU>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:52BP3ESU&lang=en

last modified: 10/23/2025 