



Siemens Low Voltage Circuit Protection OEM Disconnect & Accessories. Type: OEM DISCONNECT SWITCH Std: UL98/CSA/NFPA 79 V. Rating: 600V A. Rating: 100A No. Of poles: 3P F. Rating: 60 Hz Action: single throw Mounting: PANEL MOUNTING. O. Cycles: 10000 O. Temperature: (-20F-120F) AMBIENT TEMPERATURE Environmental Conditions: INDOOR

General technical data	
fastening method	PANEL MOUNTING
Electricity	
voltage between phase and phase rated value	600 V
Model	
product brand name	SIEMENS
product type designation	OEM DISCONNECT SWITCH
General product approval	
certificate of suitability	UL98/CSA/NFPA 79

last modified:

10/22/2025

