

UNIVERSAL CONTACTOR SUPPRESSOR

RC, 230VAC/DC/100VA/W

Art.No.: 20011

Weight: 0.030 kg

Country of origin: CZ

Model designation: RC-AD 10/230



230 V AC/DC

RC

For other configurations and voltages, please inquire.

Link to Product

Illustration



Product may differ from Image



Header

Material short text

RC-AD 10/230

Commercial data

URL Webshop

<https://shop.murrelektronik.com/20011>

GTIN	4048879020671
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-7.1	27371013
ECLASS-8.0	27371013
ECLASS-8.1	27371013
ECLASS-9.0	27371013
ECLASS-9.1	27371013
ECLASS-10.0.1	27371013
ECLASS-10.1	27371013
ECLASS-11.0	27371013
ECLASS-11.1	27371013
ECLASS-12.0	27371013
ECLASS-13.0	27371013
ECLASS-14.0	27371013
ETIM-5.0	EC002498
ETIM-6.0	EC002498
ETIM-7.0	EC002498
ETIM-8.0	EC002498
customs tariff number	85363010
EAN	4048879020671
Packaging unit	1
Electrical data	
Damping factor	1.5× UN
Holding power max.	100 W
Electrical data Input	
Input voltage AC min.	110 V
Input voltage AC max.	250 V
Input voltage DC min.	110 V
Input voltage DC max.	250 V
Installation Connection	
Connection information	self-securing cable forks
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Material housing	Plastic
Combustibility class housing (UL94)	V-0
Mechanical data Mounting data	
Height	35 mm
Width	30 mm
Depth	18 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C