

## MOTOR SUPPRESSOR

RC, 3x500VAC/4kW

Art.No.: 23001

Weight: 0.164 kg

Country of origin: CZ

Model designation: HRC 3/022-500 K



3× 500 V AC +10%

RC

Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

### [Link to Product](#)

#### Illustration



Product may differ from Image



#### Header

Material short text

HRC 3/022-500 K

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/23001">https://shop.murrelektronik.com/23001</a>
GTIN	4048879019668
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-7.1	27371013
ECLASS-8.0	27371013
ECLASS-8.1	27371013
ECLASS-9.0	27371013
ECLASS-9.1	27371013
ECLASS-10.0.1	27371013
ECLASS-10.1	27371013
ECLASS-11.0	27371013
ECLASS-11.1	27371013
ECLASS-12.0	27371013
ECLASS-13.0	27371013
ECLASS-14.0	27371013
ETIM-5.0	EC000683
ETIM-6.0	EC000683
ETIM-7.0	EC000683
ETIM-8.0	EC000683
customs tariff number	85363010
EAN	4048879019668
Packaging unit	1

**Electrical data | Supply**

Power frequency	50 ... 60 Hz
-----------------	--------------

**Electrical data | Input**

Input voltage AC	500 V
------------------	-------

**Installation**

Connection cross-section solid min.	0,75 mm <sup>2</sup>
Connection cross-section solid max.	2,5 mm <sup>2</sup>

**Installation | Connection**

Family construction form	M4
Connection information	terminal

**Installation | Pin assignment**

No. of poles	3
--------------	---

**Device protection | Media**

Flame resistance	flame retardant
------------------	-----------------

**Mechanical data | Material data**

Material housing	Plastic
Combustibility class housing (UL94)	V-0
Material potting compound	2-component epoxy

**Mechanical data | Mounting data**

Height	75 mm
Width	45 mm
Depth	42 mm

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	60 °C