

## MOTOR SUPPRESSOR

Varistor, 3x400VAC/4kW

Art.No.: 23170

Weight: 0.058 kg

Country of origin: CZ

Model designation: RC 3R-400/4-M16 X 1,5 RKS-M6

3× 400 V AC

VDR

isolated M6


Suppressors for other voltages, frequencies, and motor ratings available on request. Do not use RC motor suppressors with frequency inverters.

### Link to Product

#### Illustration



Product may differ from Image



#### Header

Material short text RC 3R-400/4-M16 X 1,5 RKS-M6

#### Commercial data

URL Webshop	<a href="https://shop.murrelektronik.com/23170">https://shop.murrelektronik.com/23170</a>
GTIN	4048879018937
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-7.1	27371013
ECLASS-8.0	27371013
ECLASS-8.1	27371013
ECLASS-9.0	27371013
ECLASS-9.1	27371013
ECLASS-10.0.1	27371013
ECLASS-10.1	27371013
ECLASS-11.0	27371013
ECLASS-11.1	27371013

ECLASS-12.0	27371013
ECLASS-13.0	27371013
ECLASS-14.0	27371013
ETIM-5.0	EC000683
ETIM-6.0	EC000683
ETIM-7.0	EC000683
ETIM-8.0	EC000683
customs tariff number	85363010
EAN	4048879018937
Packaging unit	1

**Electrical data | Supply**

Power frequency	10 ... 400 Hz
-----------------	---------------

**Electrical data | Input**

Input voltage AC	400 V
------------------	-------

**Installation**

Connection cross section max.	0,5 mm <sup>2</sup>
-------------------------------	---------------------

**Installation | Connection**

Ring terminals	M6, isolated
Length single strands	100 mm
Connection information	Single strands

**Device protection | Media**

Flame resistance	flame retardant
------------------	-----------------

**Mechanical data | Material data**

Material housing	Plastic
Combustibility class housing (UL94)	V-0
Material potting compound	2-component epoxy

**Mechanical data | Mounting data**

Height	25 mm
Width	25 mm
Depth	40 mm
Mounting method	inserted
Suitable for mounting type	Motorklemmkasten

**Environmental characteristics | Climatic**

Operating temperature min.	-20 °C
Operating temperature max.	60 °C