

POWER DISTRIBUTOR PD4 PLUG 24+E

Connector for 27680 and 27681

Art.No.: 27682

Weight: 0.320 kg

Country of origin: DE

Model designation: POWER DISTRIBUTOR PD4 PLUG 24+E

Industry female plug 24+PE

Field-wireable

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text POWER DISTRIBUTOR PD4 PLUG 24+E

Commercial data

URL Webshop	https://shop.murrelektronik.com/27682
GTIN	4048879063432
ECLASS-6.0	27279219
ECLASS-6.1	27142601
ECLASS-7.0	27142601
ECLASS-7.1	27142601
ECLASS-8.0	27142601
ECLASS-8.1	27142601
ECLASS-9.0	27142606
ECLASS-9.1	27142601
ECLASS-10.0.1	27142601
ECLASS-10.1	27142601
ECLASS-11.0	27142606
ECLASS-11.1	27142606
ECLASS-12.0	27142606
ECLASS-13.0	27142606
ECLASS-14.0	27142606

ETIM-5.0	EC002585
ETIM-6.0	EC002585
ETIM-7.0	EC002585
ETIM-8.0	EC002585
customs tariff number	85366990
EAN	4048879063432
Packaging unit	1
customs tariff number	85366990
EAN	4048879063432
Packaging unit	1

Electrical data

Security level	SELV
----------------	------

Electrical data | Supply

Operating voltage AC	50 V
Operating voltage DC	120 V
Current operating per contact max.	9 A

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed

Mechanical data | Material data

Material housing	Aluminum die casting
Coating housing	powder-coated

Mechanical data | Mounting data

Height	120 mm
Width	43 mm
Depth	70 mm
Clamping range min.	9 mm
Clamping range max.	17 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	85 °C