

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

ECLASS-13.0	27371601
ECLASS-14.0	27371601
ETIM-5.0	EC001437
ETIM-6.0	EC001437
ETIM-7.0	EC001437
ETIM-8.0	EC001437
customs tariff number	85364900
EAN	4048879021371
Packaging unit	1

Electrical data | Input

Input voltage AC	24 V
Input voltage DC	24 V

Electrical data | Output

Switching voltage AC max.	250 V
Switching voltage DC max.	30 V
Switching current max.	6 A
Switching current DC	10 mA
Switching current DC min.	100 mA
Power rating AC max.	1.500 VA
Power rating DC max.	120 W

Device protection | Electrical

Rated insulation voltage	300 V
--------------------------	-------

Mechanical data

Response time max.	8 ms
Drop-out time max.	4 ms

Mechanical data | Material data

Material contact	Ag Sn O2
------------------	----------

Mechanical data | Mounting data

Mounting method	inserted
-----------------	----------

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-40 °C ... 60 °C