

MIRO 6.2 TIMER

to be discontinued - Last Time Order: 2023-03-31

Art.No.: 3000-18512-0200030

Weight: 0.030 kg

Country of origin: CZ

Model designation: Miro 6,2 Timer 45ms



Transistor output

Impulse expansion: 40...45 ms

Spring clamp terminals

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text

Miro 6,2 Timer 45ms

Commercial data

URL Webshop

<https://shop.murrelektronik.com/3000-18512-0200030>

GTIN	4048879411608
ECLASS-6.0	27210990
ECLASS-6.1	27371790
ECLASS-7.0	27371790
ECLASS-7.1	27371790
ECLASS-8.0	27371605
ECLASS-8.1	27371605
ECLASS-9.0	27371605
ECLASS-9.1	27371605
ECLASS-10.0.1	27371605
ECLASS-10.1	27371605
ECLASS-11.0	27371605
ECLASS-11.1	27371605
ECLASS-12.0	27371605
ECLASS-13.0	27371605
ECLASS-14.0	27371605
ETIM-5.0	EC001439
ETIM-6.0	EC001439
ETIM-7.0	EC001439
ETIM-8.0	EC001439
customs tariff number	85364110
EAN	4048879411608
Packaging unit	1

Electrical data | Output

Voltage switching DC min.	2 V
Switching voltage DC max.	30 V
Switching current max.	25 mA
Switching current DC	0,1 mA
Switching frequency max.	20 Hz

Mechanical data | Mounting data

Height	91 mm
Width	6,2 mm
Depth	70 mm
Mounting method	geschnappt
Suitable for mounting type	(EN 60715), mounting rail

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Ambient temperature (storage, transport)	-40 °C

Connection type 4

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	14
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	13

Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	- A 2
Family construction form	terminal
No. of poles	1
Gender	female
Color contact carrier	black
Connection	Spring clamp terminals FK
PIN 1	+ A 1