

VALVE PLUG SUPPRESSOR FORM BI - 11MM 90°

Zener diode and LED, 24VDC/100VA/W

Art.No.: 3124133

Weight: 0.014 kg

Country of origin: CZ



Model designation: PBS-LEDY+Z-DIODE 24 V

24 V AC/DC

Z-Diode + LED

Remove plug gasket when fitting adapter. Other LED colors on request.

Note PIN arrangement (PE at cable outlet of connector). 180° turned version on request.

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text

PBS-LEDY+Z-DIODE 24 V

Commercial data

URL Webshop	https://shop.murrelektronik.com/3124133
GTIN	4048879012065
ECLASS-6.0	27371013
ECLASS-6.1	27371013
ECLASS-7.0	27371013
ECLASS-7.1	27371013
ECLASS-8.0	27371013
ECLASS-8.1	27371013
ECLASS-9.0	27371013
ECLASS-9.1	27371013
ECLASS-10.0.1	27371013
ECLASS-10.1	27371013
ECLASS-11.0	27371013
ECLASS-11.1	27371013
ECLASS-12.0	27371013
ECLASS-13.0	27371013
ECLASS-14.0	27371013
ETIM-5.0	EC000683
ETIM-6.0	EC000683
ETIM-7.0	EC000683
ETIM-8.0	EC000683
customs tariff number	85363010
EAN	4048879012065
Packaging unit	1

Electrical data

Drop-out delay time max.	20 ms
Holding power max.	50 W

Electrical data | Supply

Cut-off peak voltage max.	55 V
---------------------------	------

Electrical data | Input

Input voltage AC min.	18 V
Input voltage AC max.	32 V
Input voltage DC min.	18 V
Input voltage DC max.	32 V

Diagnostics

Status indication LED	yellow
-----------------------	--------

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data | Material data

Material housing	PA
Color housing	black
Material contact	Bronze
Coating contact	silver-plated

Mechanical data | Mounting data

Height	15 mm
Width	63 mm
Depth	21,5 mm

Environmental characteristics | Climatic

Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Housing temperature max. (EN 61347-2-13)	130 °C