

Modlight70 Pro buzzer

4 tones

Art.No.: 4000-76070-1100004

Weight: 0.065

Country of origin: ID

Model designation: Modlight70 Pro BUZZER

Buzzer modules

Link to Product

Illustration



Product may differ from Image



Commercial data	
ECLASS-6.0	27371200
ECLASS-6.1	27371237
ECLASS-7.0	27371237
ECLASS-8.0	27371237
ECLASS-9.0	27371237
ECLASS-10.1	27371237
ECLASS-11.1	27371237
ECLASS-12.0	27371237
ETIM-5.0	EC001152
customs tariff number	85318070
customs tariff number	85318070
GTIN	4048879752497
GTIN	4048879752497
Packaging unit	1
Packaging unit	1
Electrical data Supply	
Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	62,5 mA

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	PC
------------------	----

Mechanical data | Mounting data

Height	49 mm
Width	70 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	60 °C