

EUROCARD HOLDER

to be discontinued - Last Time Order: 2023-03-31

Art.No.: 4000-63011-6302470

Weight: 0.233 kg

Country of origin: CZ

Model designation: SKP 24/7-M-FK

Spring clamp terminals
24-, 7-pole M (EN 60603)
Row z, b, d



With the vertical snap adapter SASA 135 Art.-No. 63900 the holder can be mounted at right-angles on the rail.

The D2 size is for a card without a front plate.

To insert the card first press down the 2 yellow buttons. Then slide the Eurocard into the guide slots pushing until fully engaged. The card is now locked into position. It can be removed by pressing down on the 2 yellow buttons.

[Link to Product](#)

Illustration



Product may differ from Image



Header

Material short text SKP 24/7-M-FK

Side 1

No. of poles	7
Operating voltage AC	500 V
Operating current max.	4 A

Side 2

No. of poles	24
Operating voltage AC	500 V
Operating current max.	15 A

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-63011-6302470
GTIN	4048879038607
ECLASS-6.0	27260710
ECLASS-6.1	27260704
ECLASS-7.0	27440402
ECLASS-7.1	27440402
ECLASS-8.0	27440402
ECLASS-8.1	27440402
ECLASS-9.0	27460201
ECLASS-9.1	27440402
ECLASS-10.0.1	27440402
ECLASS-10.1	27440402
ECLASS-11.0	27460201
ECLASS-11.1	27460201
ECLASS-12.0	27460201
ECLASS-13.0	27460201
ECLASS-14.0	27460201
ETIM-5.0	EC002780
ETIM-6.0	EC002780
ETIM-7.0	EC002780
ETIM-8.0	EC002780
customs tariff number	85366990
EAN	4048879038607
Packaging unit	1

Installation

Connection cross-section solid max.	4 mm ²
-------------------------------------	-------------------

Installation | Pin assignment

No. of poles	7
--------------	---

Device protection | Electrical

Overvoltage category (EN 60664-1)	I
-----------------------------------	---

Device protection | Media

Flame resistance	flame retardant
------------------	-----------------

Mechanical data

Type of socket connector	M (EN 60603)
--------------------------	--------------

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	63 mm
Width	137 mm
Depth	170 mm

Mounting method	geschnappt, screwed
Suitable for mounting type	(EN 60715), mounting rail
