

MODLINK MSDD SOCKET INSERT USA NEMA 5-15

125VAC/3A with fuse

Art.No.: 4000-68000-0110000

Weight: 0.040 kg

Country of origin: DE

Model designation: Fr.Modul-AB-125-3-SC+fuse3A

USA (NEMA 5-15)

with fuse

Plug-solder connection

[Link to Product](#)**Illustration**

Product may differ from Image

**Header**

Material short text Fr.Modul-AB-125-3-SC+fuse3A

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-0110000
GTIN	4048879038195
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806

ECLASS-14.0	27182806
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
EAN	4048879038195
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	60 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	10 °C ... 60 °C
--	-----------------

Fuse

Operating voltage AC	250 V
Operating voltage DC	32 V
Nominal current	3 A
Protector type	OC - Overcurrent type
UL Use group	A
Terminals (UL 1077)	0
Tripping current (UL 1077)	1
Overload rating (UL 1077)	1
Short-circuit current rating (UL 1077)	1.0 KA, U1
UL CCN	QVNU2
UL-Standard	UL 1077
CSA Class	3215-30
CSA-Standard	CSA C22.2 No. 144.1-16

USA

Connection	Plug-solder connection
No. of poles	PE
Protection contact present	Yes
Operating voltage AC	125 V
Operating current	3 A