

MODLINK MSDD SOCKET INSERT FRANCE

Product in the discontinuation phase

Art.No.: 4000-68000-0130000

Weight: 0.057

Country of origin: FR

Model designation: UTE Informatik Steckdosenmodul (rot)

France (UTE-NF) red
with touch protection
Screw terminals

[Link to Product](#)

Illustration



Product may differ from Image



Commercial data

ECCLASS-6.0	27189217
ECCLASS-6.1	27189260
ECCLASS-7.0	27189260
ECCLASS-8.0	27189260
ECCLASS-9.0	27189260
ECCLASS-10.1	27182810
ECCLASS-11.1	27182810
ECCLASS-12.0	27182810
ETIM-5.0	EC000020
ETIM-6.0	EC000020
ETIM-7.0	EC000020
ETIM-8.0	EC000020
customs tariff number	85366990
customs tariff number	85366990
EAN	4048879038171
EAN	4048879038171
Packaging unit	1
Packaging unit	1

Mechanical data | Mounting data

The information in this Product-PDF has been compiled with the utmost care.

Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 2025-11-03

Murrelektronik Inc. | 1327 Northbrook Parkway, Suite 460 | Suwanee, GA 30024 | Fon +1 770 497-9292 | Fax +1 770 497-9391 | shop@murrinc.com | shop.murrinc.com

Height	88 mm
Width	51 mm
Depth	40 mm

Environmental characteristics | Climatic

Storage temperature min.	-10 °C
Storage temperature max.	60 °C

France (UTE-NF)

Connection cross section max.	2,5 mm ²
AWG number max.	14
Operating voltage AC	250 V
Operating current min.	10 A
Operating current max.	16 A
Connection	Spring clamp terminals FK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes