

MODLINK MSDD DATA INSERT

2xSUB-D15 female/soldering
Art.No.: 4000-68000-0510000
Weight: 0.038 kg
Country of origin: DE
Model designation: FR.MODUL 2 x 15 pol. Bu

SUB-D15; SUB-D15
2× SUB-D15 (solder connection/female)

Link to Product

Illustration



Product may differ from Image



Header

Material short textFR.MODUL 2 x 15 pol. Bu

Commercial data

URL Webshop	https://shop.murrelektronik.com/4000-68000-0510000
GTIN	4048879037952
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-7.1	27189217
ECLASS-8.0	27189217
ECLASS-8.1	27189217
ECLASS-9.0	27182806
ECLASS-9.1	27189217
ECLASS-10.0.1	27182806
ECLASS-10.1	27182806
ECLASS-11.0	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ECLASS-13.0	27182806
ECLASS-14.0	27182806

ETIM-5.0	EC002625
ETIM-6.0	EC002625
ETIM-7.0	EC002625
ETIM-8.0	EC002625
customs tariff number	85366990
EAN	4048879037952
Packaging unit	1
customs tariff number	85366990
EAN	4048879037952
Packaging unit	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	40 mm

Environmental characteristics | Climatic

Ambient temperature (storage, transport)	-30 °C
--	--------

SUB-D15

Family construction form	SUB-D15
Gender	Female
No. of poles	15
Looking techniques	Standard UNC 4-40 screw thread bolt (EN 60807)
Family type Back side	SUB-D15
Gender Rear	Solder connection
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA